



CK507WR

SELF-POWERED

- No electric service needed
- Charges by winding



HIGH-PERFORMANCE

- Runs for 9 minutes after 1 minute of winding
- High-capacity NiMH rechargeable batteries last 3 1/2 hours when fully charged



BRIGHT

- 3 Bright White Nichia® premium LEDs
- Focusing lens for bright, uniform spot



Ready if the power goes out, the CK507WR recharges by winding. Anywhere there is no electricity, you have light without worrying about batteries. High capacity NiMH rechargeable batteries can run 3 1/2 hours when fully charged and the light will run for 9 minutes after winding for only one minute.

In addition, the batteries and the LEDs never need replacing, making this light ideal as a preparedness tool.




Before Using Your Flashlight:
Please read all instructions and cautionary markings on the package and light

Product Detail:

- Designation:** Weather Ready LED Crank Light
Model: CK507WR
Color: Red and Black
Power Source: Four "AA" NiMH Rechargeable
ANSI/NEDA: 1.2H2
Lamp: Three Bright White Nichia® LEDs
Lamp Life: Lifetime (LED)
Typical Weight: 195.3 grams (6.89 oz.) (with batteries)
Dimensions (in): 7.50 x 2.50 x 1.94

Performance:



Important Notice

This datasheet contains information specific to products manufactured at the time of its publication
Contents herein do not constitute a warranty
 ©Energizer / All Rights Reserved