


SO14 Adapter (small outline)



RE932-03

- EPOXY fibre-glass FR4 1.50 mm double-sided 35 µm CU (pth)
- solder and component side with chem. NI/AU surface and solder stop mask
- pitch: 1.27 mm (153 mil)
- pins: 14
- hole dia 1.00 mm
- size 20.50 x 13.50 mm