


SO24w Adapter (small outline)



RE932-07

- EPOXY fibre-glass FR4 1.50 mm double-sided 35 µm CU (pth)
- solder and component side with chem. NI/AU surface and solder stop mask
- pitch: 1.27 mm (295 mil)
- pins: 24
- hole dia 1.00 mm
- size 25.50 x 18.50 mm