


NO	DESCRIPTION	DATE
①	DEL REF. BACKGROUND FORMAT UPDATED	07.20.09'
②	MODIFICATION CENTER CONTACT ⑥	12.30.09'



1.0 ELECTRICAL

- 1.1 FREQUENCY RANGE: DC-900 MHz
1.2 NOMINAL IMPEDANCE: 50 OHM

2.0 MATERIALS

- 2.1 BODIES: BRASS PER JIS-C3604
2.2 CENTER CONTACT: BRASS PER JIS-C3604
2.3 INSULATION: TEFLON PER ASTM D1457 AND ASTM D1710

3.0 FINISHES AND OTHERS

- 3.1 SEE BELOW TABLE FOR DETAILS.

4.0 ENVIRONMENTAL

- 4.1 OPERATING TEMPERATURE RANGE: -55° C TO +125° C

NO	DESCRIPTION	MATERIAL	Q'TY	FINISH
6	CENTER CONTACT	BRASS	1	GOLD
5	INSULATION II	TEFLON	1	NONE
4	BODY	BRASS	1	NICKEL 100μ" MIN.
3	WASHER	BRASS	1	NONE
2	INSULATION I	TEFLON	1	NONE
1	SHELL	BRASS	1	NICKEL 100μ" MIN.

APPROVED by _____ DATE: _____

DESCRIPTION		FME PLUG - MINI UHF PLUG	
製圖	DRAWN Yoko	TOLERANCE	品名 23-10 T.G.N TITLE \ROHS COMPLIANT (50Ω)
檢圖	CHECK Jacky	單位	UNIT mm(in)
認定	APPROVAL Lewis	比例	SCALE 4:1
日期	DATE 04.27.93	版次	REV. A-2
DWG.NO.		23-0042	
佳楠精密電子股份有限公司 CHIN NAN PRECISION ELECTRONICS CO.,LTD.			