



### Ovalgrip Straight Cut

#### Features and Benefits

Ovalgrip markers have been specifically designed to mark cable and wire both before and after termination.

Their oval shape means that these markers are easy to fit by hand directly onto the cable pre termination or they can be attached as an identification flag post termination using special marker Arrowtags. Arrowtags fitted with Ovalgrip are fastened using cable ties and can very easily be modified or removed without the need to uninstall the cable.

Sizes 50 and 85 can be used with Arrowtags for identifying larger cable bundles.

#### Application

Ideally suited to panel building, mass transit, utilities, telecommunications and electrical contracting.

These markers are supplied continuous on a reel (HODS).

Markers are available as a standard in yellow material marked in black and international resistor colour code. Characters are 0-9, A-Z and standard electrical symbols.

White material marked in black available on special request.


AT1 Arrowtags will fit 7 size 50 markers.

AT2 Arrowtags will fit 8 size 85 markers.

AT3 Arrowtags will fit 14 size 85 markers.



A simple idea for complex marking needs.



Ovalgrip straight cut.

Material Data	
Material	Flexible Polyvinyl Chloride, cadmium free (PVC)
Colour	White, yellow, international resistor colour code
Operating Temperature	-65 °C to +105 °C, Intermittent +135 °C
Flammability	Self extinguishing
Specification	BS 2782-540B, BS 6746C, UL224, IEC 304, IEC 757



For details on Arrowtags please see page 345.



#### Technical Table

Type	Quantity per kit	Outside Ø min.	Outside Ø max.	Length (L)	Recommended Carrier
HODS50*	1000	1.7	3.60	4.0	AT1
HODS85*	1000	1.8	6.30	4.5	AT2/AT3

All dimensions in mm. Subject to technical changes.

\* Marking text 0-9 as international resistor code, as well as A-Z, 0-9 and special characters in yellow.



HODS50 colour code



	Article-No.	Type
	531-15365	HODS50
	531-15366	HODS50
	531-15367	HODS50
	531-15368	HODS50
	531-15314	HODS50
	531-15370	HODS50
	531-15371	HODS50
	531-15372	HODS50
	531-15373	HODS50
	531-15374	HODS50

HODS85 colour code



	Article-No.	Type
	531-07728	HODS85
	531-07729	HODS85
	531-07730	HODS85
	531-07731	HODS85
	531-07732	HODS85
	531-07733	HODS85
	531-07734	HODS85
	531-07735	HODS85
	531-07736	HODS85
	531-07737	HODS85

HODS50 yellow



	Article-No.	Type
	531-15014	HODS50
	531-15024	HODS50
	531-15034	HODS50
	531-15044	HODS50
	531-15054	HODS50
	531-15064	HODS50
	531-15074	HODS50
	531-15084	HODS50
	531-15094	HODS50
	531-15104	HODS50
	531-15114	HODS50
	531-15124	HODS50
	531-15134	HODS50
	531-15144	HODS50
	531-15154	HODS50
	531-15164	HODS50
	531-15174	HODS50
	531-15184	HODS50
	531-15194	HODS50
	531-15204	HODS50
	531-15214	HODS50
	531-15224	HODS50
	531-15234	HODS50
	531-15244	HODS50
	531-15254	HODS50
	531-15264	HODS50
	531-00451	HODS50
	531-00452	HODS50
	531-00175	HODS50
	531-00176	HODS50
	531-00174	HODS50
	531-15274	HODS50
	531-15284	HODS50
	531-15294	HODS50
	531-15304	HODS50
	531-15314	HODS50
	531-15324	HODS50
	531-15334	HODS50
	531-15344	HODS50
	531-15354	HODS50
	531-15364	HODS50

HODS85 yellow



	Article-No.	Type
	531-07935	HODS85
	531-07936	HODS85
	531-07937	HODS85
	531-07938	HODS85
	531-07939	HODS85
	531-07940	HODS85
	531-07941	HODS85
	531-07942	HODS85
	531-07943	HODS85
	531-07944	HODS85
	531-07945	HODS85
	531-07946	HODS85
	531-07947	HODS85
	531-07948	HODS85
	531-07949	HODS85
	531-07950	HODS85
	531-07951	HODS85
	531-07952	HODS85
	531-07953	HODS85
	531-07954	HODS85
	531-07955	HODS85
	531-07956	HODS85
	531-07957	HODS85
	531-07958	HODS85
	531-07959	HODS85
	531-07960	HODS85
	531-07924	HODS85
	531-07923	HODS85
	531-07961	HODS85
	531-00386	HODS85
	531-00384	HODS85
	531-07925	HODS85
	531-07926	HODS85
	531-07927	HODS85
	531-07928	HODS85
	531-07732	HODS85
	531-07930	HODS85
	531-07931	HODS85
	531-07932	HODS85
	531-07933	HODS85
	531-07934	HODS85