





Pin heatsinks / **ICK S R 32,5 x 10**

Ø 32,5 x 10 mm, pin heatsinks round

**Parameters of article ICK S R 32,5 x 10**

<b>Bauform</b>	Rund
<b>R<sub>th</sub> [K/W]</b>	5.54
<b>dissipation loss [W]</b>	9
<b>mounting method</b>	therm. conductive foil / therm. cond. adhesive
<b>socket</b>	universal
<b>suitable for processor type</b>	universal
<b>Ø [mm]</b>	32.5
<b>height [mm]</b>	10
<b>plate thickness [mm]</b>	3
<b>weight [g]</b>	9.7

**Accessories/ related articles**

Thermally conductive foil both sides adhesive / **WLFT 404 D 32**

Thermally conductive foil both sides adhesive / **WLFT 405 D 32**