


## LED machine luminaire




**SPOT LED 003 - MCTFL 3 N**

connected load	100-240 V; 50/60 Hz
fitted with	3 x Power-LED
work equipment	electronic plug-in transformer
mains lead	approx. 3.0 m; European/American plug (N1-15P)
luminaire body	
material	aluminium
surface	anodised
tubular sections	
material	flexible metal tube
weight (net)	approx. 1,6 kg
fastening	screw-down flange~magnetic base (accessory)~table clamp (accessory)~wall bracket (accessory)
technology	switchable
usage	switch
lamp cover	glass screen
balance of articulation joints	friction
system of protection	IP 40 (65)
class of protection	II
colour luminaire body	black
colour of tubular sections	Jet black
special features	Spot with a 10° angle of radiation,
article no.	112462007



E<sub>min</sub>: 164 lx  
 E<sub>m</sub>: 3056 lx  
 E<sub>max</sub>: 19959 lx



measuring conditions: d=50cm

