

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0987891088](#)
Status: **Active - Custom**
Description: NSCC single part, Non Sealed, 1.5mm, Female Housing, 10 Circuits, Dual Row, Gray

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Crimp Housings
Series	98789
Application	Power
Product Name	NSCC

Physical

Circuits (maximum)	8
Color - Resin	Gray
Gender	Receptacle
Glow-Wire Compliant	No
Lock to Mating Part	Yes
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	4.25mm (.167")
Pitch - Termination Interface	6.00mm (.236")
Polarized to Mating Part	Yes
Ports	1
Stackable	No
Temperature Range - Operating	-40°C to +120°C

Material Info

Old Part Number	07318EV8F8
-----------------	------------

Reference - Drawing Numbers

Sales Drawing	SD-98789-001
---------------	--------------



image - Reference only

EU RoHS

**ELV and RoHS
Compliant**
**REACH SVHC
Not Reviewed**
**Low-Halogen Status
Not Reviewed**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of
 Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
 non-product compliance questions.

Search Parts in this Series

[98789Series](#)

Mates With

[987881081](#) , [Link987881088](#)