



RAL 7035



RAL 7032

## Outlet grilles

- Delivered with G2 M1 synthetic standard filter.
- Material: Injected thermoplastic (ASA PC), self-extinguishing according to UL94 V0.

Dimensions (mm)		IP	Reference RAL 7035
Total (external)	Cut-out		
137 × 117 × 13	92 × 92	54	NSYCAG92LPF
170 × 150 × 15	125 × 125	54	NSYCAG125LPF
268 × 248 × 18	223 × 223	54	NSYCAG223LPF
336 × 316 × 18	291 × 291	54	NSYCAG291LPF

## Replacement grilles in RAL 7032

- External part of the grille (for fan or outlet grille) for changing the colour to RAL 7032.


Dimensions (mm) Total (external)	IP	Reference RAL 7032
137 × 117 × 13	54	NSYCAG92LPC
170 × 150 × 15	54	NSYCAG125LPC
268 × 248 × 18	54	NSYCAG223LPC
336 × 316 × 18	54	NSYCAG291LPC



## Filters

Concept	For fans and grilles		Pack.	Reference
	External dimensions (mm)	Cut-out (mm)		
G2 M1 synthetic standard filters	137 × 117	92 × 92	5	NSYCAF92
	170 × 150	125 × 125	5	NSYCAF125
	268 × 248	223 × 223	5	NSYCAF223
	336 × 316	291 × 291	5	NSYCAF291
Filters for greasy environments G2 M1	170 × 150	125 × 125	5	NSYCAF125O
	268 × 248	223 × 223	5	NSYCAF223O
	336 × 316	291 × 291	5	NSYCAF291O
G3 M1 synthetic fine filters	170 × 150	125 × 125	5	NSYCAF125T
	268 × 248	223 × 223	5	NSYCAF223T
	336 × 316	291 × 291	5	NSYCAF291T
Stainless-steel anti-insect filters	137 × 117	92 × 92	1	NSYCAF92M
	170 × 150	125 × 125	1	NSYCAF125M
	268 × 248	223 × 223	1	NSYCAF223M
	336 × 316	291 × 291	1	NSYCAF291M

8



## Anti-vandalism kit

- Prevents the grille from being opened from the outside.
- The unlocking thumbwheel is accessed from the inside of the wall-mounting enclosure.
- RAL 7011 colour (same material as the grille: ASA PC).

Minor packaging	Reference
2	NSYCAAPV