

GENTECH INTERNATIONAL LTD

Grangestone Industrial Estate  
Girvan, Ayrshire KA26 9PS  
United Kingdom

Telephone: +44 1465 713581  
Fax: +44 1465 714974

E-Mail: [info@gentechsensors.com](mailto:info@gentechsensors.com)  
Web Site [www.gentechsensors.com](http://www.gentechsensors.com)

## POSITION SENSOR

PS2 Series – Surface Mount Fitting

### PS2011

UL Listed Sensor

#### Design Features

- Adjustable with XY axis using the PM101/102 magnets
- Cable wiring from the Left of the package
- Repeatability of operation
- Shunt or direct magnet operation
- Multiple Mode of Operation



#### Product Comments

- Robust Nylon Housing
- Normally Open
- Surface Mounted by fixing screws
- Fully encapsulated
- Matching Package Operating Magnet PM101 or PM102
- UL Listed file E153493


#### Typical Applications

- Door Interlocks
- Hook Switches
- Security Systems
- Safety Interlocks
- Position Indication



#### Material, Design and Operation

Mounting	Surface
Material:	Nylon 6.6
Contact Form:	Form A - SPST
Contact Material:	Ruthenium
Maximum Switching Volts:	250 VAC
Maximum Switching Current:	1.0 A
Switching Action:	SPST
Maximum Power:	15 Watts
Housing Temperature Range °C:	100
Connection Type:	Stripped Cables
Cable Type:	2 x 24AWG, 7/0.2mm PVC Insulated 0.5M long
Operating Temperature Range °C:	70
Actuation Method:	Magnetic
Mounting Shock:	50g for 11ms duration
Mounting Vibration:	35g up to 500Hz
Magnetic Approach:	Direct Axis, Parallel Axis
Approvals:	UL

## Line Drawing



Recommended mounting screw:  
Pan head self tapping screw  
No.4 x 9.5mm (0.37) long



Maximum operate distance (all models)  
D1 = 10mm (0.39)  
D2 = 3mm (0.12)

MODES OF OPERATION  
1 Side by side  
2 End to end  
3 Magnetic shunt

