

Handheld Instruments

EA3010 Enhanced Handheld Anemometer

This handheld anemometer is ideal for the outdoor professional. It has the capability to measure wind speed and wind chill and fits perfectly in your pocket!



Features

- Displays current wind speed
- Displays maximum wind speed since power on
- Displays average wind speed since power on
- Wind speed unit selectable between knots, meters per second, miles per hour and kilometers per hour
- Beaufort scale is displayed in bar graph (0-12)
- Displays the current temperature
- Displays the current wind chill
- Temperature selectable to °F or °C
- Backlight with auto off feature
- Battery saving auto off feature
- Neck band included for easy carrying

Specification

- Maximum measured speed: 67 mph
- Minimum measured speed: 0.44 mph
- Resolution-wind speed: 0.1 for all units
- Temperature measuring range: -21.8 to 138.2°F/ -29.9 to 59°C
- Resolution-temperature : 0.2°F/ 0.1°C
- Power requirements : 1 CR2032 button cell