





S 1/2" drive wobble extensions


- Square drive rounded profile gives 8° working angle.
- Useful where access is restricted.

	\square "	D mm	B mm	L mm	$\Delta\Delta$ g
S.208S	1/2	23	16,5	75	130
S.210S	1/2	23	16,5	130	225
S.215S	1/2	23	16,5	250	420


**S 1/2" drive extensions**

- ▷ Performance : to ISO 3316, DIN 3123, NF ISO 3316.
- Chrome finish.


	\square "	D mm	B mm	L mm	$\Delta\Delta$ g
S.206	1/2	23	16,5	52,5	90
S.208	1/2	23	16,5	75,0	130
S.210	1/2	23	16,5	130,0	225
S.215	1/2	23	16,5	250,0	420
S.217	1/2	23	16,5	500,0	840

**1/2" universal joint****S.240A**

- ▷ Performance : to ISO 3316, DIN 3123, NF ISO 3316.
 - Spring-stiffened joint.
 - Stays in position when reaching for fasteners.
 - Significant time savings.
- $\Delta\Delta$: 150 g.

**1/2" to 3/8" coupler****S.230**

- ▷ Performance : to ISO 3316, DIN 3123, NF ISO 3316.
 - 1/2" female to 3/8" male square drive.
 - For adapting sockets and accessories \square 3/8".
 - Max. torque 212 N.m.
- $\Delta\Delta$: 55 g.

**1/2" to CDX® coupler****S.231**

- 1/2" female to CDX® male square drive.
- $\Delta\Delta$: 65 g.

