

TECHNICAL DATA

Model No: MW206**Type** Regulated DC/DC Adaptor**Electrical Data**

| | | |
|-------------------|----------------------------|--------------------------------|
| Input | Input Voltage/Frequency | 12-24V DC |
| | Input Power | — |
| Output | Rated Output Voltage | 1.5V,3V,4.5V,6V,7.5V,9V 12V |
| | Rated Output Load Current | Max 1200mA |
| | Rated Output Power | 14.4VA MAX |
| Resistance | Insulation Resistance | — |
| Protection | Thermal Protection | — |
| | Withstand Voltage (Hi-Pot) | — |

Mechanical Data

| | |
|------------------------|---|
| Supply Connection Type | CP1 |
| Output Plug Dimensions | 2.5mm 3.5mm 3.5×1.35mm 5.0×2.1mm 5.5×2.5mm 2.35×0.75mm |
| Polarity | Reversible |
| Unit Weight | 172g |
| Dimensions (mm) | 128x52x34mm |