

Ratchet cable cutter - KNIPEX 95 31

Mfr#: 95 31 250



Description

One-handed operation thanks to ratchet mechanism. Cuts smoothly and cleanly, without deforming the cable. Also suitable for stripping cable sheath. Great power transfer, low weight and compact construction allow this tool to be used in even the tightest of spaces. The swivel blade can be unlocked in any cutting position just by pressing down with your thumb. **Not suitable for wire rope or steel wire**

Highlights

- Up to max. 32 mm width of fuselage

Features:

- Ratchet mechanism
- Two-speed tooth gear drive
- Special quality tool steel
- Strong grip sleeves
- Fixed sleeve with stand for placing tool when cutting.

Technical data

Length:	250 mm
Max. Cutting value:	Ø 32 mm/ 240 mm/ MCM500
Type:	95 31 250
Material suitability:	Suitable for aluminium and copper cables, single- and multistrand · Not suitable for steel wire and hard-drawn copper wire.