

## Facom J.17 3/8" Drive OGV Socket 17mm



### Description

**Higher torque without damage to fasteners !**

The OGV® profile is achieved by a succession of curves instead of the flats found in conventional sockets.

**More powerful tightening:** Larger contact area between socket and fastener minimizes stress.

**Less wear:** Torque is transmitted through the fastener flats instead of the corners.

**Increased durability:** Stress concentration in the corners is eliminated.

### Technical specification:

17mm AF 12 point socket with 3/8" drive

Performance: to ISO 2725-1, DIN 3124, NF ISO 2725-1.