

Facom J.13LA 3/8"Drive Long Reach 12-Point OGV Socket 13mm



Description

Higher torque without damage to fasteners !

The OGV® profile is achieved by a succession of curves instead of the flats found in conventional sockets.

More powerful tightening: Larger contact area between socket and fastener minimizes stress.

Less wear: Torque is transmitted through the fastener flats instead of the corners.

Increased durability: Stress concentration in the corners is eliminated.

Technical specification:

13mm AF 12 point long reach socket with 3/8" drive

Performance: to ISO 2725-1, DIN 3124, NF ISO 2725-1.