

## **Facom J.17LA 3/8"Drive Long Reach 12-Point OGV Socket 17mm**



### **Description**

**Higher torque without damage to fasteners !**

The OGV® profile is achieved by a succession of curves instead of the flats found in conventional sockets.

**More powerful tightening:** Larger contact area between socket and fastener minimizes stress.

**Less wear:** Torque is transmitted through the fastener flats instead of the corners.

**Increased durability:** Stress concentration in the corners is eliminated.

### **Technical specification:**

17mm AF 12 point long reach socket with 3/8" drive

Performance: to ISO 2725-1, DIN 3124, NF ISO 2725-1.