

TECHNICAL DATA

Model Number: MD150D050UK/D+**Type** Multi--Voltage AC/DC Adaptor**Electrical Data**

| | | |
|-------------------|----------------------------|--|
| Input | Input Voltage/Frequency | 230V/50Hz |
| | Input Power | 16W |
| Output | Rated Output Voltage | 15V |
| | Rated Output Load Current | 500mA |
| | Rated Output Power | 7.5 VA |
| Resistance | Insulation Resistance | 100MΩ(measured with 500V DC voltage) |
| Protection | Thermal Protection | Thermal fuse:125□/2A |
| | Withstand Voltage (Hi-Pot) | AC 3750V 50Hz for 1minute or AC4000V 2seconds |

Mechanical Data

| | |
|------------------------------|-------------------|
| Supply Connection Type | UK |
| Primary Turns & Wire Gauge | 1550T/0.13mm |
| Secondary Turns & Wire Gauge | 100T/0.55mm |
| Core Size | 48mm×26mm |
| Output Plug Dimensions | 5.0×2.1 ×12mm |
| Polarity | CENTER POSITIVE |
| Unit Weight | 455g |
| Dimensions | 75(L)×58(W)×80(H) |