

TECHNICAL DATA

Model Number: MC120D050UK/D+**Type** Multi--Voltage AC/DC Adaptor**Electrical Data**

Input	Input Voltage/Frequency	230V/50Hz
	Input Power	12W
Output	Rated Output Voltage	12V
	Rated Output Load Current	500mA
	Rated Output Power	6 VA
Resistance	Insulation Resistance	100MΩ(measured with 500V DC voltage)
Protection	Thermal Protection	Thermal fuse:125□/2A
	Withstand Voltage (Hi-Pot)	AC 3750V 50Hz for 1minute or AC4000V 2seconds

Mechanical Data

Supply Connection Type	UK
Primary Turns & Wire Gauge	2050T/0.11mm
Secondary Turns & Wire Gauge	119T/0.45mm
Core Size	41mm×26mm
Output Plug Dimensions	5.0×2.1 ×12mm
Polarity	CENTER POSITIVE
Unit Weight	332g
Dimensions	67(L)×50(W)×80(H)