

# TECHNICAL DATA

**Model Number:** MB060D050UK/D+

**Type** Single-Voltage AC/DC Adaptor

## Electrical Data

<b>Input</b>	Input Voltage/Frequency	230V/50Hz
	Input Power	7.9W
<b>Output</b>	Rated Output Voltage	6V
	Rated Output Load Current	500mA
	Rated Output Power	3.0 VA
<b>Resistance</b>	Insulation Resistance	100MΩ(measured with 500V DC voltage)
<b>Protection</b>	Thermal Protection	Thermal fuse:125□/2A
	Withstand Voltage (Hi-Pot)	AC 3750V 50Hz for 1minute or AC4000V 2seconds

## Mechanical Data

Supply Connection Type	UK
Primary Turns & Wire Gauge	3220T/0.09mm
Secondary Turns & Wire Gauge	115T/0.45mm
Core Size	41mm×16mm
Output Plug Dimensions	5.0×2.1 ×12mm
Polarity	CENTER POSITIVE
Unit Weight	249g
Dimensions	59(L)×50(W)×72(H)