


**Longer Lasting Labels**

Brother's unique, patented TZ tapes are designed to be extra hard wearing. Tests have shown that these scratch-proof labels can withstand heavy abrasion, electrical resistance and lengthy exposure to chemicals, sunlight, water and extreme temperatures from -50°C to 300°C. Brother laminated tapes consist of six layers of materials, resulting in a thin, extremely strong label. Characters formed with thermal transfer ink are actually printed onto the underside of the laminate. Sandwiched between two layers of PET (polyester film) this lets you create characters that are virtually indestructible.

**Brother Laminate Tape Construction**




LAMINATED BROTHER TAPES WITH PATENTED BROTHER UNDER-TAPE PRINTING

**Tape Options**

- Options include standard laminated tape including fluorescent and transparent options. Specialist tapes include Non-laminated, Matt, Strong Adhesive, and Flexi ID. All are available in varying widths, character and tape colour options.
- Tape widths of 6, 9 and 12mm
- Standard tape length of 8m\*

\*Providing approximately 100 labels. (based on 10 characters & standard label length 8cm)

**Tape Widths**



**Tape Colours**



NB. Not all tape colours are available in all countries.

**Technical Information**

Hardware		Firmware	
<b>Housing Dimensions</b>	108mm(W) x 196mm(D) x 55mm(H) (with cutter lever)	<b>Built in Fonts</b>	Helsinki & Oklahoma
<b>Housing Design</b>	Slim Handheld	<b>Characters</b>	241
<b>Housing Weight</b>	335g (without batteries and tape cassette)	<b>Symbols</b>	59
<b>Housing Color</b>	Blue	<b>No. of lines printable</b>	Max. 2 lines
<b>Key Board</b>	ABCD	<b>Text Buffer</b>	55 characters
<b>Number of Keys</b>	49 keys	<b>Memory</b>	Yes (Store./Recall./Delete) up to 9 files, Max 300 characters
<b>Cutter</b>	Manual Cut	<b>Type Styles</b>	Normal / Bold / Outline / Shadow / Italic / Italic Bold / Italic Outline / Italic Shadow / Vertical / Mirror
<b>Power (not included)</b>	AAA sized Alkaline Batteries x 6pcs or AC Adapter (Model G or G1)	<b>Framing &amp; Fill Pattern</b>	5 kinds (Off/Undl/Round/Banner/Wooden/Vine)
<b>LCD</b>	8 chrs x 1 line	<b>Repeat Printing</b>	Yes (1-9)
<b>Item Included</b>	Users Guide 12mm x 5m Black on White Starter Tape	<b>Underline</b>	Yes
<b>Tape Type</b>	TZ-tape	<b>Tape Margin Settings</b>	Yes (Full/Half/Narrow/Chain)
<b>Tape Size</b>	6 / 9 / 12mm	<b>Numbering</b>	Yes (0-9)
<b>Print Head</b>	180 dpi	<b>Battery Weak Indication</b>	Yes
<b>Max. Print Height</b>	9mm	<b>LCD Language Change</b>	Yes (English/French/German)
<b>Print Speed</b>	10mm / sec.	<b>Auto Power Off</b>	Yes
		<b>Print Image (Preview)</b>	Yes

Contact:



**Brother International Europe Ltd**  
Audenshaw, Manchester M34 5JE  
Tel: 0870 830 4020 (National Rate Call) Fax: 0870 830 4031  
www.brother.co.uk

Your calls to us may be monitored or recorded for training purposes. All specifications correct at time of printing. Brother is a registered trademark of Brother Industries Ltd. Brand product names are registered trademarks or trademarks of their respective companies.

ZLFTPT1000U1



Always at your side



**Preview screen** enables you to check your label before you decide to print

Powered by AC adapter for even greater economy or 6 x AAA batteries, (neither included)

**Separate ABC 123 keys** simple, clear keyboard makes it so easy to use

**Shortcut Feature** save time when formatting your labels

**Slim hand-held design** a stylish machine that is light yet durable

**Manual built-in cutter** - every label is cut to size

### The P-touch 1000 from Brother.

An easy-to-use, hand-held labelling machine for the office or home, that produces a wide variety of professional quality labels made to last. It's the P-touch 1000 electronic labelling system from Brother.

### Organising your world has never been easier

Whether you'd like to organise your workplace or simply sort things out around the home, it shouldn't be complicated. With the P-touch 1000 you just key in the word or number, choose the style, and then print. With Brother's professional quality TZ tapes you know these are labels that will last.

The P-touch 1000 is ideal for creating labels for any of the following:

### Always at your side

- FILES AND FOLDERS
- CDS AND STATIONERY
- COMPUTER EQUIPMENT
- TOOLS AND GARDENING EQUIPMENT
- CLOTHING
- HOBBIES AND DIY

### Printing that puts you in control

- Large printing area makes every label easier to read and printing on two lines means you can include as much detail as you'd like
- Choose from two different font styles **Oklahoma** **Helsinki**
- Choose up to ten different type styles plus framing and underlining
- Access over 50 symbols by pressing the symbol key € @ % © → ↩



### Long lasting labels that always look good

If you label something, you want the label to look good and to last. Brother's TZ labels are specifically designed to be hardwearing

- P-touch labels are ideal for use both inside and outside in all weather conditions. They are able to withstand temperatures from -50°C to 300°C, this means the labels are resistant to freezing conditions and direct sunlight so they won't fade.
- Available in a range of colours



As well as durable TZ tape, the range also includes the following tapes:

- Strong Adhesive Tape** - gives improved adhesion for those even more demanding applications and environments. In tests, this tape has shown improved performance on materials including: stainless steel, glass, PVC, acrylic, polypropylene and polyester-coated wood
- Fabric Iron-On Tape** - produces washable cloth labels that can be attached onto various fabrics by using an iron. This tape is ideal for labelling uniforms, work wear, bedding and table cloths



Stationery



Storage



Valuables



CDs

