

## 19" Surge Protection & Filters



A range of high quality surge protected and filtered sockets for mounting within rack enclosures or for general use within offices or retail environments.

- Professional range of Surge Protected sockets and Filter circuitry
- Total absorbing capacity 520 Joules
- Anodized aluminium case
- Phosphor bronze contacts for long term reliability
- High grade flame retardant grey nylon for all mouldings
- Various sizes available in horizontal or vertical mount sockets
- Tested and approved by BSI to BS3456, BS7002, BS415 and relevant parts of BS1363/A
- All products with 2m cable and moulded 13 amp plug

Manufacturers Part Number	RMH-SFJ6	RMH-SFJ10
Length, lead	2 m	2 m
Connector type A	UK Mains Plug	UK Mains Plug
Connector type B	6 x Sockets	10 x Sockets