



Basic Specification


| | | |
|---|---|-------------|
| Model: | | CR1620 |
| Nominal Voltage: | | 3.0Volts |
| Nominal Capacity: | (@0.2mA Discharge Current to 2.0V cut-off, +23°C) | 70mAh |
| Standard Discharge Current: | | 0.2mA |
| Maximum recommended current under continuous discharge: | | 2.0mA |
| Maximum recommended current under pulse discharge: | | 10.0mA |
| Operational temperature range: | | -20°C~+60°C |
| Nominal Weight: | | 1.3g |

Electrical Characteristics



blister card

dimensions: 50 x 70mm
total weight: approx 2,5g

| | | |
|---|---------------------------------------|-------------------------|
|  | specifications for model/type: | CR 1620 Lithium battery |
| | Ansmann drawing number / part number: | 5020072 |
| | | |
| | drawn by / date: | Brandt / 14.07.2006 |