




## BASIC SPECIFICATION

Model:		CR2430
Nominal Voltage:		3.0Volts
Nominal Capacity:	(@0.5mA Discharge Current to 2.0V cut-off, +23°C)	270mAh
Standard Discharge Current:		0.5mA
Maximum recommended current under continuous discharge:		3.0mA
Maximum recommended current under pulse discharge:		20.0mA
Operational temperature range:		-20°C ~ +60°C
Nominal Weight:		4.3g

**minimum discharge time at 1,5kOhm load (E.V.2,0V)** 125h

## ELECTRICAL CHARACTERISTICS



	specifications for model/type:	CR 2430 Lithium battery
	Ansmann drawing number / part number:	5020092
	drawn by / date:	Brandt / 06.07.2006