


"Y" Blindé 360° avec câble : Mâle droit / femelles droites - "Y" with cable "Y" mit Kabel

5, 4, 3 contacts/contacts/Kontakte



Références - Part numbers - Teil N°

5 contacts - contacts - Kontakte	YM1252FFD05***B
4 contacts - contacts - Kontakte	YM1252FFD04***B
3 contacts - contacts - Kontakte	YM1242FFD03***B

B : Type de câble - Type of cable - Kabeltyp

B : Blindé à 360°

Ø D voir p 53

*** L : 003 = 0,3 m ; 006 = 0,6 m
008 = 0,8 m ; 010 = 1m

Longueur à la demande disponible -
Also available in length specified by customer -
Länge auch nach Kundenwunsch lieferbar

Accessoires / Accessories / Zubehör p 104

Caractéristiques générales

- Cordons surmoulés de type M12, mâles et femelles (5, 4 & 3 contacts Ø1 en laiton dorés).
- Continuité de blindage à 360°
- Isolants en thermoplastique PA chargé Fibre de verre.
- Surmoulage des fiches M12 en TPU.
- Ecrou et Reprise de blindage en Laiton Nickelé.
- Encombrements conforme à la M12
- Etanchéité IP 67
- Version droite et coudée (fiches M12)
- Verrouillage à visser
- Température d'utilisation : -30°C / +70°C

Main characteristics

- Overmoulded junction cable M12, male and female (5, 4 and 3 contacts dia.1mm brass with gold finish).
- Shielded continuity
- Thermoplastic insulator PA with glass fiber
- Overmoulding to the M12 plug in TPU
- Nut and shielding in brass with nickel finish
- Dimensional characteristics according to M12 norm
- Protection class : IP 67
- Straight and angled M12 plug
- Locking by screwing
- Static temperature range : -30°C to +70°C