



Material Nickel plated brass
INOX (1.4305)



Further sizes upon request

IG	H mm	mm	Number Ms	H mm	mm	Number INOX
M 12 x 1,5	2,8	15	1.161.1200.50	3	17	1.161.1200.58
M 16 x 1,5	2,8	19	1.161.1600.50	3	19	1.161.1600.58
M 20 x 1,5	3,0	23	1.161.2000.50	3	24	1.161.2000.58
M 25 x 1,5	3,5	29	1.161.2500.50	4	27	1.161.2500.58
M 32 x 1,5	4,0	36	1.161.3200.50	5	36	1.161.3200.58
M 40 x 1,5	4,5	45	1.161.4000.50	5	46	1.161.4000.58
M 50 x 1,5	5,5	55	1.161.5000.50	5	55	1.161.5000.58
M 63 x 1,5	6,0	70	1.161.6300.50	6	70	1.161.6300.58
PG 7	2,8	15	1.161.0700.01	2,8	17	1.161.0700.08
PG 9	2,8	18	1.161.0900.01	2,8	22	1.161.0900.08
PG 11	3,0	21	1.161.1100.01	3	22	1.161.1100.08
PG 13,5	3,0	23	1.161.1300.01	3	24	1.161.1300.08
PG16	3,0	26	1.161.1600.01	3	27	1.161.1600.08
PG 21	3,5	32	1.161.2100.01	3,5	32	1.161.2100.08
PG 29	4,0	41	1.161.2900.01	4	41	1.161.2900.08
PG 36	5,0	51	1.161.3600.01	5	50	1.161.3600.08
PG 42	5,0	60	1.161.4200.01			
PG 48	5,5	64	1.161.4800.01			

