

# Hand Held Hanging Scales

For use where conventional pan weighing is inappropriate or difficult



Ideal for large containers, sacks and packages. Having a large stainless steel hook the **A393 Series** of electronic hanging scales offer a choice of 3 capacities, 15kg, 25kg and 50kg. Constructed from robust ABS plastic, each hanging scale has a large hi-contrast 14mm LCD screen.

- 15kg, 25kg and 50kg capacities.
- Overload protection to 25% of capacity.
- Virtually instant readings.
- Function indicators.
- Tare facility over full range.
- 14mm Hi-contrast LCD display.
- Low battery warning.
- ISO 9000 Certificate of Calibration is available.
- Optional stainless steel support and pan.



## Technical Specifications

Model	A393-01	A393-00	A393-50
Range	15Kg	25Kg	50Kg
Resolution	20g	50g	50g
Accuracy	±0.5%	±0.5%	±0.5%
Power	9V PP3 battery		
Dimensions	255 x 90 x 28mm, including handle and hook.		

Model No.	Description	Price 1-3	Price 4+
A393-01	15Kg Hanging Scales	£50.00	£47.50
A393-00	25Kg Hanging Scales	£52.50	£49.88
A393-50	50Kg Hanging Scales	£55.00	£52.25
ACAL-HS	ISO 9000 4 Point Calibration Certificate	£55.00	£52.50
AHS-SP	Hanging Support and Pan	£45.00	£42.75
ALR-61	9V PP3 Alkaline Battery	£0.98	£0.94