

ANSMANN - 5035202 - ACCU, NIMH, 1.2V, AA2850 MAH, PK2



Specifications:

- ACCU, NIMH, 1.2V, AA2850 MAH, PK2
- Battery Size:AA
- Battery Capacity:2850mAh
- Output Voltage Fixed:1.2V
- Battery Technology:Nickel Metal Hydride
- External Height:50.35mm
- External Width:14.3mm
- Battery IEC Code:HR6
- External Length / Height:50.35mm