



ALAN BUTCHER COMPONENTS LTD



Alan Butcher Components Ltd
 Unit 1 Beechwood
 Clump Farm Industrial Estate
 Tin Pot Lane Blandford
 Dorset DT11 7TD

Telephone 01258 456360
 Facsimile 01258 459194
 sales@abcomponents.co.uk
 www.abcomponents.co.uk

ABI-010-RC SPECIFICATION SHEET

Features:

- Colour: Black
- Housing Material: Noryl
- Built in oscillating circuit
- Wave solderable and washable

All data at 25°C unless otherwise specified.

SPECIFICATIONS	ABI-010-RC Electro-mechanical Indicator
Rated Voltage	12VDC
Operating Voltage	8~16VDC
Rated Current at rated voltage	30mA
Sound Output at 10cm, at rated voltage	≥85dB
Resonant Frequency at rated voltage	2300 ± 300Hz
Operating Temperature	-20 ~ +70°C
Storage Temperature	-30 ~ +80°C
Weight	2g

DIMENSIONS: (UNIT: mm, TOLERANCE: ±0.5mm)

