

350W Jigsaw



Model: D01666

- Powerful 350W motor
- Variable speed
- Bevel cuts up to 45° right or left
- Convenient lock-on button reduced user fatigue
- Dust cover
- Built-in dust port for easy vacuum attachment
- Hex wrench stores conveniently on the tool
- Will take U-Type fitting blades

Technical Data

| | |
|-------------------|------|
| Wattage | 350W |
| Cutting Capacity: | |
| Wood | 55mm |
| Steel | 6mm |

618772 549682

| Mfrs. List No. | Order Code | Price Each | | |
|-------------------|------------|------------|---|---|
| | | + | + | + |
| D01666 | 185-0622 ● | - | - | - |