

850W SDS Hammer Drill



Model: D01661

- Rotation stop for light chiselling
- SDS Plus pull back chuck
- Dust guard on chuck
- Multi-position side handle
- Supplied with 3 x SDS drills 8, 10, 12 x 150mm, 1 x point chisel, 1 x flat chisel and a blow moulded carry case

Technical Data	
Wattage	850W
Voltage	230V
Chuck Type	SDS Plus
No Load Speed	850rpm
Hammer	Yes
Impact Rate	3150BPM
Drilling Capacity ⌀ :	
Wood	40mm
Steel	13mm
Masonry	26mm
Weight	4.7kg

618697 549793

Mfrs. List No.	Order Code	Price Each	
		+	+
D01661	185-0619 ●	--	--