

datasheet for KUN 30 Au  
article number: 931804704



<b>product description:</b>	order number: 931 804-704
<b>description:</b>	Shatter-proof, flexible, insulated coupling for a 4 mm diameter plug and solder connection up to a cable cross-section of 2.5 mm <sup>2</sup> . Gold-plated brass socket.
<b>typ:</b>	KUN 30 gruen/green Au
<b>system:</b>	4 mm system
<b>order number:</b>	931 804-704
<b>color</b>	
<b>other color versions:</b>	
<b>technical data</b>	
<b>type of contact:</b>	unsprung socket
<b>type of termination:</b>	solder
<b>rated voltage:</b>	DC 60 V
<b>rated current:</b>	16 A
<b>contact resistance:</b>	2 mOhm
<b>material</b>	
<b>contact material:</b>	brass
<b>contact surface material:</b>	gold
<b>housing material:</b>	PVC-P
<b>environmental conditions:</b>	
<b>temperature range:</b>	-25 °C to +70 °C
<b>drawing</b>	