


datasheet for PKI 10 A Au
 article number: 930103702



product description:	order number: 930 103-702
description:	Pole terminal with claw edge and captive insulated head and insulated ring. 4 mm diameter gold -plated brass threaded bolt with 2 mm diameter transverse hole. For insulated, non-rotating installation in equipment chassis and switchpanels with a wall thickness.
typ:	PKI 10 A blau/blue Au
system:	4 mm system
order number:	930 103-702
color	
other color versions:	
technical data	
type of contact:	spring unloaded socket
type of termination:	M 4 thread
rated voltage:	DC 60 V
rated current:	35 A
contact resistance:	1,5 mOhm
mounting:	screw
material	
contact material:	brass
contact surface material:	gold- plated
housing material:	PF
connecting nut material:	AuCo0,2
environmental conditions:	
temperature range:	-25 °C to +100 °C
inflammable class:	
housing:	94 V-0
drawing	

