



datasheet for SEB 2600 G M4
 article number: 972354106



| | |
|----------------------------------|---|
| product description: | order number: 972 354-106 |
| description: | Safety built-in socket, 4 mm diameter, touch-protected, M 4 threaded connection and soldering hole, gold-plated brass. For installation into switchpanels and equipment chassis with wall thicknesses up to 6 mm. Accessory BES 1000. Installation hole: 12.2 mm diameter. Tightening torque: 50 Ncm. |
| typ: | SEB 2600 G M4 grau/grey |
| system: | 4 mm safety system |
| order number: | 972 354-106 |
| color |  |
| other color versions: |  |
| technical data | |
| measurement category | CAT III |
| norm | DIN EN 61010-031 |
| type of contact: | unsprung socket |
| type of termination: | screw / solder |
| rated voltage: | AC/DC 1000 V |
| rated current: | 32 A |
| contact resistance: | 5 mOhm |
| mounting: | screw |
| material | |
| contact material: | brass |
| contact surface material: | gold |
| housing material: | PA |
| connecting nut material: | brass nickel-plated |
| environmental conditions: | |
| temperature range: | -40°C to +80°C |
| flammable class: | |
| housing: | 94 V-2 |
| drawing | |

