



datasheet for SEB 2600 G M4  
 article number: 972354107



<b>product description:</b>	order number: 972 354-107
<b>description:</b>	Safety built-in socket, 4 mm diameter, touch-protected, M 4 threaded connection and soldering hole, gold-plated brass. For installation into switchpanels and equipment chassis with wall thicknesses up to 6 mm. Accessory BES 1000. Installation hole: 12.2 mm diameter. Tightening torque: 50 Ncm.
<b>typ:</b>	SEB 2600 G M4 weiß/white
<b>system:</b>	4 mm safety system
<b>order number:</b>	972 354-107
<b>color</b>	
<b>other color versions:</b>	
<b>technical data</b>	
<b>measurement category</b>	CAT III
<b>norm</b>	DIN EN 61010-031
<b>type of contact:</b>	unsprung socket
<b>type of termination:</b>	screw / solder
<b>rated voltage:</b>	AC/DC 1000 V
<b>rated current:</b>	32 A
<b>contact resistance:</b>	5 mOhm
<b>mounting:</b>	screw
<b>material</b>	
<b>contact material:</b>	brass
<b>contact surface material:</b>	gold
<b>housing material:</b>	PA
<b>connecting nut material:</b>	brass nickel-plated
<b>environmental conditions:</b>	
<b>temperature range:</b>	-40°C to +80°C
<b>flammable class:</b>	
<b>housing:</b>	94 V-2
<b>drawing</b>	

