

datasheet for MSEB 2610 F 2,8 Au
 article number: 975455704



product description:	order number: 975 455-704
description:	Miniature - safety built-in socket, 2 mm diameter, touch protected, 2,8 mm flat plug connection, gold-plated brass. For installation into switch- panels and equipment chassis with a wall thickness up to 8 mm. Installation hole: 8 mm diameter
typ:	MSEB 2610 F 2,8 Au grün/green
system:	2 mm safety system
order number:	975 455-704
technical data	
measurement category	CAT III
norm	IEC 61010
type of contact:	spring unloaded socket
type of termination:	flat plug 2,8 x 0,8 mm
rated voltage:	AC/DC 1000 V
rated current:	10 A
contact resistance:	2 mOhm
material	
contact material:	brass
contact surface material:	gold- plated
housing material:	PA 6.6
connecting nut material:	gold- plated
environmental conditions:	
temperature range:	-25 °C to +70 °C
inflammable class:	
housing:	UL 94 V-2
drawing	
	