

datasheet for MSEB 2610 F 2,8 Au  
 article number: 975455706



<b>product description:</b>	order number: 975 455-706
<b>description:</b>	Miniature - safety built-in socket, 2 mm diameter, touch protected, 2,8 mm flat plug connection, gold-plated brass. For installation into switch- panels and equipment chassis with a wall thickness up to 8 mm. Installation hole: 8 mm diameter
<b>typ:</b>	MSEB 2610 F 2,8 Au grau/grey
<b>system:</b>	2 mm safety system
<b>order number:</b>	975 455-706
<b>technical data</b>	
<b>measurement category</b>	CAT III
<b>norm</b>	IEC 61010
<b>type of contact:</b>	spring unloaded socket
<b>type of termination:</b>	flat plug 2,8 x 0,8 mm
<b>rated voltage:</b>	AC/DC 1000 V
<b>rated current:</b>	10 A
<b>contact resistance:</b>	2 mOhm
<b>material</b>	
<b>contact material:</b>	brass
<b>contact surface material:</b>	gold- plated
<b>housing material:</b>	PA 6.6
<b>connecting nut material:</b>	gold- plated
<b>environmental conditions:</b>	
<b>temperature range:</b>	-25 °C to +70 °C
<b>flammable class:</b>	
<b>housing:</b>	UL 94 V-2
<b>drawing</b>	
	