




## BASIC SPECIFICATION

Model:		CR1220
Nominal Voltage:		3.0Volts
Nominal Capacity:	(@0.2mA Discharge Current to 2.0V cut-off, +23°C)	40mAh
Standard Discharge Current:		0.2mA
Maximum recommended current under continuous discharge:		1.0mA
Maximum recommended current under pulse discharge:		5.0mA
Operational temperature range:		-20°C~+60°C
Nominal Weight:		0.8g

## ELECTRICAL CHARACTERISTICS



	specifications for model/type:	CR 1220 Lithium battery
	Ansmann drawing number / part number:	5020062
	drawn by / date:	Brandt / 06.07.2006