

Farnell Module Maintenance

Module: **527216** | Width: **85.00mm** | Operator: **ZEBISCHA** | Print date & time: **10 Dec 2008 ● 15:13**

ExternalRefs:	MAMRefs:
ModuleRefs:	TreeNodeRefs:
ProdRefs: 42742999	Primary ProdRefs: 42742999
SecondaryProdRefs: 42742999	SecProdRefsbymodname: Metabo 12 Volt Cordless Drill / Screwdriver BZ 12 SP Li #G

Division: Master Modules Publication: PRODUCT PORTFOLIO Book: TOOLS Section: Air Tools Product Group: Farnell InOne Product SubGroup: LOCAL GERMAN Group: NEW INTRODUCTIONS (00/00/03) Module: Metabo 12 Volt Cordless Drill / Screwdriver BZ 12 SP Li #G	IndexType: Descriptive Index Primary word: Cordless Secondary Word: Screwdriver Primary word: Drills Secondary Word: Cordless Secondary Word: Screwdriver Secondary Word: Set Primary word: Tools Secondary Word: Drills and Accessories
--	---

12 Volt Cordless Drill/Screwdriver BS 12 SP

incl. Accessories and tool box

metabo



- Variospeed (V) electronics for infinitely variable speed change
- 20-level adjustable torque, plus drilling level
- Clockwise and anticlockwise rotation
- Quick stop for rapid fastening of screws
- Quick-action keyless chuck and spindle stop gear for convenient one-hand tool change: Metabo "Quick"
- T-handle for optimum centre of gravity, especially for screws
- Fatigue-free operation due to perfect ergonomoy
- High service life due to 3-level planetary metal gears

- Gentle, spring-supported gear change
- Built-in collector fan to prevent overheating
- Bit depot for 2 bits
- Composability of charger and battery packs (within a volt-category)
- Easy and quick change of battery pack
- AIR COOLED quick charger AC 30 for reduced charge time. Load time ca. 30 minutes (1.4 Ah)

Supplied with: 2 NiCd battery packs (12 V/ 1.4 Ah), "AIR COOLED" quick charger AC 30 Plus, carry case, accessorie set (over 100 pieces)

Technical data		Technical data	
Type of battery pack	NiCd	Drilling capacity in wood	20 mm / 16mm
Battery pack voltage:	12V	No load speeds:	0 - 400 / 0 - 1.450 / min
Capacity of battery pack:	1.4Ah	Drilling spindle thread:	1/2" - 20 UNF
Max. torque, soft:	18 Nm	Chuck capacity:	1.0 - 10mm
Max. torque, hard:	35 Nm	Weight (with battery pack):	1.7kg
Drilling capacity in steel	10mm / 5mm		

527216

Mfrs List No.	Order Code	+	+	+
BZ 12 SP NICD	167-0538	--	--	--