

## SPECIFICATION OF HR-AU

Type: Nickel-Metal Hydride Battery		Size : A	
Capacity <sup>1)</sup>	Typical	2700mAh	
	Minimum	2450mAh	
Nominal Voltage		1.2V	
Charging Current x Time		Fast Charge <sup>2)</sup> 2700mA x about 1.1h	
Ambient Temp.	Charge Condition	Fast Charge <sup>2)</sup> 0~40 °C	
	Discharge Condition		0~50 °C
	Storage Condition	~30days	-20~50 °C
		30~90days	-20~40 °C
		90days~1year	-20~30 °C
Internal Impedance <sup>3)</sup> (after discharge to E.V.=1.0V)		About 20mOhm (at 1000Hz)	
Weight <sup>4)</sup>		about 40g	
Size <sup>4)</sup> : (Diameter) x (Height)		17.0 x 50.0 mm	

1)Charge: 0.1C×16h, Discharge: 0.2C(E.V.=1.0V) at 25°C

2)Use recommended charging system.

3)After a few charge and discharge cycles under the above 1) condition.

4)With tube.