



SANYO

Cadnica

Cell Type N-1300SCR


Specifications




Nominal Capacity		1300mAh	
Nominal Voltage		1.2V	
Charging Current	Standard	130mA	
	Quick	390mA	
	Fast	2000mA	
Charging Time	Standard	14 to 16Hrs.	
	Quick	4 to 6Hrs.	
	Fast	about 1Hr.	
Ambient Temperature	Charge	Standard	0°C to +45°C [+32°F to 113°F]
		Quick	10°C to +45°C [+50°F to 113°F]
		Fast	5°C to +40°C [+41°F to 104°F]
	Discharge		-20°C to +60°C [-4°F to 140°F]
	Storage		-30°C to +50°C [-22°F to 122°F]
Internal Impedance (Av.) (at 50% discharge)		4.0mΩ (at 1000Hz)	
Weight		52g/1.83oz	
Dimensions(D)×(H) (with tube)		22.9 ⁰ ₋₁ × 43.0 ⁰ _{-1.2} mm	
		0.90 ⁰ _{-0.04} × 1.69 ⁰ _{-0.05} inch	

Typical Characteristics


Charge (5 sells pack)




Discharge (at high rate)




Cell Capacity (at various discharge rate)



Discharge (at high rate)



Discharge (at low rate)



Temperature (Charge & Discharge)

