


datasheet for MA 1
 article number: 930317800



product description:	order number: 930 317-800
description:	Miniature alligator clip with high strength insulation and nickel-plated brass/bronze jaws. The part of the jaws (fine wire section) allows a secure contact to be made when clamping even the thinner wire. Capable of clamping flat components (soldering eyes) and wire up to a maximum diameter of 4mm.
typ:	MA 1 schwarz / black
system:	2mm system
order number:	930 317-800
clamping range:	conductor with maximum Ø 4mm
color	
other color versions:	
technical data	
type of contact:	to clamp
type of termination:	2mm socket
rated voltage:	DC 60V
contact resistance:	5mOhm
material	
contact material:	brass/bronze
contact surface material:	nickel
housing material:	PA
environmental conditions:	
temperature range:	from -25°C to +100°C
inflammable class:	
housing:	94 HB
drawing	
	