


Mounted points

Schleifstifte

Meules sur tige

Muelas de corindón



Aluminium oxide / Aluminiumoxid / Oxyde d'aluminium / Óxido de aluminio

Pink / Rosa / Rose / Rosa

Shape B / Form B / Forme B / Forma B

For actual size shape reference see pages 121-124

Für genaue Größenformkennung siehe Seiten 121-124

Pour le gabarit grandeur nature, voir pages 121-124

Para la referencia a tamaño / forma real, véanse las páginas 121-124

Maximum permissible speeds based on a maximum overhang of 13mm

Maximal zulässige Drehzahl basiert auf einem maximalen Überhang von 13mm

Vitesses maximales permises, pour un porte-à-faux maximum de 13mm

Velocidades máximas permisibles sobre la base de un saliente máximo de 13mm

	shape/Form/Forme/Forma	B41	B42	B44	B46	B52	B53	B62	B71
	Part Nr	GHB04103PKM	GHB04203PKM	GHB04403PKM	GHB04603PKM	GHB05203PKM	GHB05303PKM	GHB06203PKM	GHB07103PKM
d1	16mm	13mm	6mm	3mm	10mm	6mm	13mm	16mm	
l1	16mm	19mm	10mm	8mm	19mm	16mm	10mm	3mm	
d2	3mm	3mm	3mm	3mm	3mm	3mm	3mm	3mm	
	33,750	33,750	68,400	105,000	45,370	60,000	41,020	59,680	
	10	10	10	10	10	10	10	10	
IPC Code	51	51	51	51	51	51	51	51	

	shape/Form/Forme/Forma	B81	B91	B92	B97	B98	B101	B103	B104
	Part Nr	GHB08103PKM	GHB09103PKM	GHB09203PKM	GHB09703PKM	GHB09803PKM	GHB10103PKM	GHB10303PKM	GHB10403PKM
d1	19mm	13mm	6mm	3mm	3mm	16mm	16mm	8mm	
l1	5mm	16mm	6mm	10mm	6mm	18mm	5mm	10mm	
d2	3mm	3mm	3mm	3mm	3mm	3mm	3mm	3mm	
	47,750	34,500	81,370	105,000	105,000	33,750	59,680	68,400	
	10	10	10	10	10	10	10	10	
IPC Code	51	51	51	51	51	51	51	51	

	shape/Form/Forme/Forma	B121	B122	B123	B131	B132	B133	B135
	Part Nr	GHB12103PKM	GHB12203PKM	GHB12303PKM	GHB13103PKM	GHB13203PKM	GHB13303PKM	GHB13503PKM
d1	13mm	10mm	5mm	13mm	10mm	10mm	6mm	
l1	13mm	10mm	5mm	13mm	13mm	10mm	13mm	
d2	3mm	3mm	3mm	3mm	3mm	3mm	3mm	
	45,370	61,650	104,250	34,500	45,370	54,000	60,000	
	10	10	10	10	10	10	10	
IPC Code	51	51	51	51	51	51	51	