

## FEATURES AND SPECIFICATIONS



## PowerCat 6 FTP Patch Cords PVC

### Features and Benefits

Molex Premise Networks PowerCat 6 FTP patch cords are manufactured using high quality shielded four pair Category 6 stranded cable. Available in a range of colours and lengths, PowerCat 6 FTP patch cords are pre-terminated with RJ45 shielded plugs and feature cable strain relief boots with a plug latch protection cap.

Suitable for high speed data transmission, PowerCat 6 FTP patch cords have been designed to exceed the highest electrical performance standards in the industry and have been independently tested and verified by ETL SEMKO for Category 6 component compliance.

- Shielded 4 pair stranded cable
- Pre-terminated with WEBW shielded plugs
- Strain relief boots
- Independently tested

### Compliant With

TIA/EIA-568-B.2-1, FCC Part 68 (Plug dimensions and tolerances), ISO 60603-7, ISO 11801:2002, EN 50173:2002

### Approvals

UL  
CSA  
ETL Verified for Category 6 Component Compliance

### Technical Information

#### Mechanical Characteristics - Cable

Conductor size: 26 AWG stranded bare copper  
Screen Material: Aluminium/polyester shield with tinned copper drain wire  
Max O.D.: 6.0mm  
Jacket: PVC  
Temperature range: -20°C to +60°C


#### Mechanical Characteristics - Plug

Operating life: Minimum 750 insertion cycles  
Contact material: Copper alloy  
Contact plating: 1.25 micrometres Au/Ni

Plug dimensions & tolerances compliant with FCC Part 68 and IEC 60603-7

#### Electrical Characteristics - Plug

Max voltage: 150 VAC (max)  
Max current: 1.5A @ 25°C  
Operating temperature: -40°C to 85°C



## ORDERING INFORMATION

Order No.	Description
PCD-00304-0*	Patch Cord FTP 568A/B - 0.5m C6
PCD-00305-0*	Patch Cord FTP 568A/B 1m C6
PCD-00306-0*	Patch Cord FTP 568A/B 1.5m C6
PCD-00307-0*	Patch Cord FTP 568A/B 2m C6
PCD-00308-0*	Patch Cord FTP 568A/B 2.5m C6
PCD-00309-0*	Patch Cord FTP 568A/B 3m C6
PCD-00310-0*	Patch Cord FTP 568A/B 3.5m C6
PCD-00311-0*	Patch Cord FTP 568A/B 4m C6
PCD-00312-0*	Patch Cord FTP 568A/B 5m C6
PCD-00313-0*	Patch Cord FTP 568A/B 6m C6
PCD-00314-0*	Patch Cord FTP 568A/B 7m C6
PCD-00315-0*	Patch Cord FTP 568A/B 8m C6
PCD-00316-0*	Patch Cord FTP 568A/B 9m C6
PCD-00317-0*	Patch Cord FTP 568A/B 10m C6

\* Colour Options: C=Red, E=Grey, H=Blue, J=Green, K=Yellow



## MOLEX PREMISE NETWORKS

Corporate Headquarters  
Tel: 1-866-733-6659  
www.molexpn.com

European Headquarters  
Tel: 44 (0) 1489 527111  
www.molexpn.co.uk

Pac Rim Headquarters  
Tel: 61 3 9971 7111  
www.molexpn.com.au



3 metre Category 6 FTP Patch Cord Typical (in - dB)

NEXT			Return Loss	
Frequency (MHz)	NEXT Limit	NEXT	Return Loss Limit	Return Loss
1	65	93.0	19.9	43.1
4	65	83.9	21.6	35.1
8	65	79.3	22.5	28.2
10	65	78.4	22.8	26.9
16	61.5	78.8	23.4	26.5
20	59.6	75.7	23.7	28.9
25	57.7	70.8	24.0	39.1
31.25	55.7	66.4	23.0	31.0
62.5	49.9	66.3	20.0	26.3
100	46	59.0	18.0	26.6
200	40.3	56.1	14.9	33.2
250	38.5	44.2	14.0	22.1

**MOLEX PREMISE NETWORKS**

Corporate Headquarters  
 Tel: 1-866-733-6659  
 www.molexpn.com

European Headquarters  
 Tel: 44 (0) 1489 527111  
 www.molexpn.co.uk

Pac Rim Headquarters  
 Tel: 61 3 9971 7111  
 www.molexpn.com.au