

L693 CERAMIC, FILLED FUSE





These size 0 (32mm x 6.3mm), sand filled, standard fuse links are of the highest quality, having a category of duty of 440 Va.c., 230 Vd.c. (maximum prospective overload 33,000 A at 0.3 pf and 440 Va.c. or 230 Vd.c.) (Time constant 0.015ms.) Minimum life is 1,000 hours continuous at rated current at temperatures up to 35°C. 1,000 hours continuous at 80% rated current at temperatures beyond 35°C up to 85°C.

TEMPERATURE RANGE:	-60°C to +85°C
SPECIFICATION:	DEF-63-A
HUMIDITY CLASSIFICATION:	DEF-133
MARKING:	Body marked with rating and Joint Services' reference number
WEIGHT:	2.6g
APPROVALS:	N/A

ORDERING REFERENCE: L693/CURRENT RATING IN AMPERES

AVAILABLE IN 250 mA, 500 mA, 1A, 2A, 3A, 5A, 7A, 10A



BLP reserve the right to change without prior notice the information contained within this leaflet

BLP Components Ltd., Exning Road, Newmarket, Suffolk, CB8 0AX, England
Tel: +44 (0)1638 665161 Fax: +44 (0)1638 660718 email: sales@blpcomp.com <http://www.blpcomp.com>