

# TECHNICAL DATA

**Model Number:** 501UK/6XC6**Type** Multi-Voltage AC/DC Regulated Adaptor**Electrical Data**

<b>Input</b>	Input Voltage/Frequency	230V/50Hz
	Input Power	15.4W
<b>Output</b>	Rated Output Voltage	1.5/3.0/4.5/6.0/7.5/9.0/12V
	Rated Output Load Current	500mA
	Rated Output Power	6VA(max)
<b>Resistance</b>	Insulation Resistance	100M $\Omega$ (measured with 500V DC voltage)
<b>Protection</b>	Thermal Protection	Thermal fuse:125 $\square$ /2A
	Withstand Voltage (Hi-Pot)	AC 3750V 50Hz for 1minute or AC4000V 2seconds

**Mechanical Data**

Supply Connection Type	UK
Primary Turns & Wire Gauge	1675T/0.12mm
Secondary Turns & Wire Gauge	48-58-68-78-88-98-115 T/0.50 mm
Core Size	48mm×24mm
Output Plug Dimensions	2.5mm      3.5mm      3.5×1.35mm 5.0×2.1mm 5.5×2.5mm 2.35×0.75mm
Polarity	Can be selected
Unit Weight	522g
Dimensions	92X63X85mm

Model: 501UK/6XC6

# **TECHNICAL DATA**

page2