



AMPROBE®

ACD-6 Pro & ACD-6 TRMS Pro
1000 A Digital Clamp-ons



Patent # D472,482

**Simple to operate and well-suited for most basic applications.
The TRMS version improves performance and reliability.**

- TRMS (ACD-6 TRMS Pro only)
- Auto and manual ranging
- Relative zero mode
- Auto power off
- Data hold
- Carrying case included
- Large, easy to read LCD display
- Diode Test
- Audible continuity
- Accommodates conductors up to 1.77" (45mm) in diameter
- Safety CAT III 600V



| FEATURES | ACD-6 Pro | ACD-6 TRMS Pro | ACCURACY |
|------------|---|----------------|--|
| TRMS | N/A | Yes | |
| AC Voltage | 4.000 / 40.00 / 400.0 / 600V | | ± (2% Rdg + 5 LSD) @ 4V to 400V ranges, 50 and 60 Hz** |
| DC Voltage | 400.0 mV 4.000 / 40.00 / 400.0 / 600V | | ± (1.7% Rdg + 3 LSD) @ 4V to 400V ranges** |
| Resistance | 400.0 Ω 4.000 / 40.00 / 400.0 kΩ 4.000 / 10.00 MΩ | | ± (1.0% Rdg + 4 LSD) @ 400Ω to 400 kΩ ranges** |
| AC Current | 400.0 / 1000 A | | ± (1.5% Rdg + 5 LSD) @ 50 and 60 Hz |

| OPTIONAL ACCESSORIES | PART NUMBER |
|--|-------------|
| Line splitter (Energizer) | A47L |
| 3000A AC Flexible Clamp-on Attachment | ACF-3000 AK |
| 5000A Clamp-on Current Transformer (50 to 1) | CT50-1 |
| 3000A Clamp-on Current Transformer (50 to 1) | CT50-2 |
| Single Input Thermocouple Temperature Attachment | TMA-K |
| Alligator Clips (For test leads) | VRC-320 |

| REPLACEMENT PARTS (supplied with product) | PART NUMBER |
|--|--|
| Test leads with set of alligator clips (alligator clips are not supplied with product) | MTL-90B |
| Carrying case | SV-U |
| Instruction Manual | www.AMPROBE.com |



Miramar, FL 33025 • Toll Free: 800-327-5060 • Phone: 954-499-5400 • Fax: 954-499-5418 • www.Amprobe.com

www.AMPROBE.com