



## TH-3 Relative Humidity Temperature Meter

- Dual display
- Relative function monitors humidity and temperature changes
- Extended probe stem to easily access air ducts
- Min/Max readings
- Data Hold
- Capacitive sensor with protective cover
- Auto Power off
- Soft Carrying Case
- One-year warranty

### No hassle warranty

*No waiting.*

*No shipping charges.*



Our commitment to high-quality products and customer service is demonstrated by our industry exclusive "No Hassle" warranty. In the unlikely event that an Amprobe Test Tool requires warranty service, any of our local dealers are authorized to replace it, on the spot.

(note: \$500 MSLP limit)

The TH-3 uses a precision capacitance sensor to deliver accurate performance with long term stability. This high accuracy instrument measures the full range of relative humidity from 0% to 100% and features an exceptionally wide ambient temperature measurement range from -20 °C (-4 °F) to 60 °C (140 °F). The sensor is mounted on a long shaft extending from the top surface of the unit, making probing into ductwork and hard to reach areas more easy. The large LCD displays two measurements simultaneously with a full range of display options including Hold, Min, Max, and Relative. The TH-3 is a complete package and comes with soft carrying case, sensor cover, battery and manual.

#### Included Accessories

Soft carrying case, sensor cover, battery (installed), users manual

**General Specifications**

Display	Dual display
Operating Conditions:	0 °C to 40 °C
Storage Conditions:	-10 °C to 60 °C; <70 % RH
Altitude	Up to 2000 meters
Sample rate	2.5 times per second
Battery	9 V Battery, NEDA 1604 or JIS 006P or IEC6F22
Battery life	85-hours continuous (with alkaline battery)
Dimension	240 x 54 x 34 mm (9.5 x 2.1 x 1.3 in.)
Weight	Approximately 180 g (6.4 oz.)

**Technical Specifications**

Function	Range	Accuracy
<b>Measurement Ranges</b>		
Humidity	0 % RH to 100 % RH	
Range accuracy	5 % RH to 95 % RH: <5%RH, >95% RH	±3 % RH @ 23 °C ±5 % RH @ 23 °C
Temperature Coefficient:		0.1 x specified accuracy/ °C <23 °C, >23 °C
Resolution	0.1 %RH	
Temperature (Dry Bulb)	-20 °C to 60 °C: -4 °F to -140 °F	±0.8 °C ±1.6 °F
Resolution	0.1 °C/0.1 °F	
<b>Response time (in slowly moving air)</b>		
Humidity	180 sec	
Temperature	10 sec	

**Amprobe® Test Tools**  
 website: [www.Amprobe.com](http://www.Amprobe.com)  
 email: [info@amprobe.com](mailto:info@amprobe.com)  
 Everett, WA 98203  
 Tel: 877-AMPROBE

**Amprobe® Test Tools Europe**  
 In den Engematten 14  
 79286 Glottertal, Germany  
 Tel.: +49 (0) 7684 8009 - 0