

**SANDVIK BELZER****Flexible workshop mirror**

Finish: mirror casing natural finish, chromed flexible shaft.
Material: aluminium mirror casing, flexible brass shaft.
 The desired mirror position can be adjusted at the handle.

2510



Product code	EAN code 731415+		Mirror mm	Length of handle mm	
2510	1064297	1	50x70	500	280

Universal inspection mirror, with clip and light

Finish: adjustable mirror.
Material: stainless steel mirror casing, extension of PVC tube.
 With clip and light, can be used as pocket mirror after removing PVC tube.

5526



Product code	EAN code 731415+		Mirror Ø mm	Length of handle mm	L mm	
5526	1401047	1	30	190	300	90

Flexible inspection mirror, with light

Finish: plastic handle, magnifying mirror.
Material: BRASS, flexible steel spiral of stainless steel.
 With light.

5523



Product code	EAN code 731415+		Mirror Ø mm	L mm	
5523	1087104	1	23	490	125

Small mirror

Finish: nickel-plated, blue sheath.
Material: BRASS.
 Magnifying, with plastic handle, length 80 mm. For work on circuit boards with mirror protection pouch.

5515L



Product code	EAN code 731415+		Mirror Ø mm	L mm	
5515L	1481568	5	18	175	15