

# GAL16V8Z GAL16V8ZD

Zero Power E<sup>2</sup>CMOS PLD

#### Features


- ZERO POWER E<sup>2</sup>CMOS TECHNOLOGY
- 100µA Standby Current
- Input Transition Detection on GAL16V8Z
- Dedicated Power-down Pin on GAL16V8ZD
- Input and Output Latching During Power Down
- HIGH PERFORMANCE E<sup>2</sup>CMOS TECHNOLOGY
- 12 ns Maximum Propagation Delay
- Fmax = 83.3 MHz
- 8 ns Maximum from Clock Input to Data Output
- TTL Compatible 16 mA Output Drive
- UltraMOS<sup>®</sup> Advanced CMOS Technology
- E<sup>2</sup> CELL TECHNOLOGY
- Reconfigurable Logic
- Reprogrammable Cells
- 100% Tested/100% Yields
- High Speed Electrical Erasure (<100ms)
- 20 Year Data Retention
- EIGHT OUTPUT LOGIC MACROCELLS
  - Maximum Flexibility for Complex Logic Designs
  - Programmable Output Polarity
  - Architecturally Similar to Standard GAL16V8
- PRELOAD AND POWER-ON RESET OF ALL REGISTERS — 100% Functional Testability
- APPLICATIONS INCLUDE:
  - Battery Powered Systems
  - DMA Control
  - State Machine Control
  - High Speed Graphics Processing
- ELECTRONIC SIGNATURE FOR IDENTIFICATION

#### Description

The GAL16V8Z and GAL16V8ZD, at 100  $\mu$ A standby current and 12ns propagation delay provides the highest speed and lowest power combination PLD available in the market. The GAL16V8Z/ZD is manufactured using Lattice Semiconductor's advanced zero power E<sup>2</sup>CMOS process, which combines CMOS with Electrically Erasable (E<sup>2</sup>) floating gate technology.


The GAL16V8Z uses Input Transition Detection (ITD) to put the device in standby mode and is capable of emulating the full functionality of the standard GAL16V8. The GAL16V8ZD utilizes a dedicated power-down pin (DPP) to put the device in standby mode. It has 15 inputs available to the AND array.

Unique test circuitry and reprogrammable cells allow complete AC, DC, and functional testing during manufacture. As a result, Lattice Semiconductor delivers 100% field programmability and functionality of all GAL products. In addition, 100 erase/write cycles and data retention in excess of 20 years are specified.



#### **Pin Configuration**

#### **DIP/SOIC**



Copyright © 1997 Lattice Semiconductor Corp. All brand or product names are trademarks or registered trademarks of their respective holders. The specifications and information herein are subject to change without notice.

LATTICE SEMICONDUCTOR CORP., 5555 Northeast Moore Ct., Hillsboro, Oregon 97124, U.S.A. Tel. (503) 268-8000; 1-800-LATTICE; FAX (503) 268-8556; http://www.latticesemi.com

#### December 1997



## GAL16V8Z/ZD Ordering Information


#### GAL16V8Z: Commercial Grade Specifications

| Tpd (ns) | Tsu (ns) | Tco (ns) | lcc (mA) | <b>lsb (</b> μ <b>A)</b> | Ordering #    | Package            |
|----------|----------|----------|----------|--------------------------|---------------|--------------------|
| 12       | 10       | 8        | 55       | 100                      | GAL16V8Z-12QP | 20-Pin Plastic DIP |
|          |          |          | 55       | 100                      | GAL16V8Z-12QJ | 20-Lead PLCC       |
|          |          |          | 55       | 100                      | GAL16V8Z-12QS | 20-Lead SOIC       |
| 15       | 15       | 10       | 55       | 100                      | GAL16V8Z-15QP | 20-Pin Plastic DIP |
|          |          |          | 55       | 100                      | GAL16V8Z-15QJ | 20-Lead PLCC       |
|          |          |          | 55       | 100                      | GAL16V8Z-15QS | 20-Lead SOIC       |

#### GAL16V8ZD: Commercial Grade Specifications

| Tpd (ns) | Tsu (ns) | Tco (ns) | lcc (mA) | <b>lsb (</b> μ <b>A)</b> | Ordering #     | Package            |
|----------|----------|----------|----------|--------------------------|----------------|--------------------|
| 12       | 10       | 8        | 55       | 100                      | GAL16V8ZD-12QP | 20-Pin Plastic DIP |
|          |          |          | 55       | 100                      | GAL16V8ZD-12QJ | 20-Lead PLCC       |
| 15       | 15       | 10       | 55       | 100                      | GAL16V8ZD-15QP | 20-Pin Plastic DIP |
|          |          |          | 55       | 100                      | GAL16V8ZD-15QJ | 20-Lead PLCC       |

## Part Number Description





#### **Output Logic Macrocell (OLMC)**

The following discussion pertains to configuring the output logic macrocell. It should be noted that actual implementation is accomplished by development software/hardware and is completely transparent to the user.

There are three global OLMC configuration modes possible: **simple**, **complex**, and **registered**. Details of each of these modes is illustrated in the following pages. Two global bits, SYN and ACO, control the mode configuration for all macrocells. The XOR bit of

each macrocell controls the polarity of the output in any of the three modes, while the AC1 bit of each of the macrocells controls the input/output configuration. These two global and 16 individual architecture bits define all possible configurations in a GAL16V8Z/ZD. The information given on these architecture bits is only to give a better understanding of the device. Compiler software will transparently set these architecture bits from the pin definitions, so the user should not need to directly manipulate these architecture bits.

#### **Compiler Support for OLMC**

Software compilers support the three different global OLMC modes as different device types. Most compilers also have the ability to automatically select the device type, generally based on the register usage and output enable (OE) usage. Register usage on the device forces the software to choose the registered mode. All combinatorial outputs with OE controlled by the product term will force the software to choose the complex mode. The software will choose the simple mode only when all outputs are dedicated combinatorial without OE control. For further details, refer to the compiler software manuals.

When using compiler software to configure the device, the user must pay special attention to the following restrictions in each mode.

In **registered mode** pin 1 and pin 11 are permanently configured as clock and output enable, respectively. These pins cannot be configured as dedicated inputs in the registered mode. In **complex mode** pin 1 and pin 11 become dedicated inputs and use the feedback paths of pin 19 and pin 12 respectively. Because of this feedback path usage, pin 19 and pin 12 do not have the feedback option in this mode.

In **simple mode** all feedback paths of the output pins are routed via the adjacent pins. In doing so, the two inner most pins (pins 15 and 16) will not have the feedback option as these pins are always configured as dedicated combinatorial output.

When using the standard GAL16V8 JEDEC fuse pattern generated by the logic compilers for the GAL16V8ZD, special attention must be given to pin 4 (DPP) to make sure that it is not used as one of the functional inputs.



#### **Registered Mode**

In the Registered mode, macrocells are configured as dedicated registered outputs or as I/O functions.


Architecture configurations available in this mode are similar to the common 16R8 and 16RP4 devices with various permutations of polarity, I/O and register placement.

All registered macrocells share common clock and output enable control pins. Any macrocell can be configured as registered or I/O. Up to eight registers or up to eight I/Os are possible in this mode. Dedicated input or output functions can be implemented as subsets of the I/O function.

Registered outputs have eight product terms per output. I/Os have seven product terms per output.

Pin 4 is used as dedicated power-down pin on GAL16V8ZD. It cannot be used as functional input.


The JEDEC fuse numbers, including the User Electronic Signature (UES) fuses and the Product Term Disable (PTD) fuses, are shown on the logic diagram on the following page.



Note: The development software configures all of the architecture control bits and checks for proper pin usage automatically.



#### **Registered Mode Logic Diagram**





#### **Complex Mode**

In the Complex mode, macrocells are configured as output only or  $\ensuremath{\mathrm{I/O}}$  functions.


Architecture configurations available in this mode are similar to the common 16L8 and 16P8 devices with programmable polarity in each macrocell.

Up to six I/Os are possible in this mode. Dedicated inputs or outputs can be implemented as subsets of the I/O function. The two outer most macrocells (pins 12 & 19) do not have input capability. Designs requiring eight I/Os can be implemented in the Registered mode.

All macrocells have seven product terms per output. One product term is used for programmable output enable control. Pins 1 and 11 are always available as data inputs into the AND array.

Pin 4 is used as dedicated power-down pin on GAL16V8ZD. It cannot be used as functional input.

The JEDEC fuse numbers including the UES fuses and PTD fuses are shown on the logic diagram on the following page.




Note: The development software configures all of the architecture control bits and checks for proper pin usage automatically.



#### Complex Mode Logic Diagram

**DIP, SOIC & PLCC Package Pinouts** 





#### Simple Mode

In the Simple mode, macrocells are configured as dedicated inputs or as dedicated, always active, combinatorial outputs.


Architecture configurations available in this mode are similar to the common 10L8 and 12P6 devices with many permutations of generic output polarity or input choices.

All outputs in the simple mode have a maximum of eight porduct terms that can control the logic. In addition, each output has programmable polarity.

Pins 1 and 11 are always available as data inputs into the AND array. The center two macrocells (pins 15 & 16) cannot be used in the input configuration.

Pin 4 is used as dedicated power-down pin on GAL16V8ZD. It cannot be used as functional input.

The JEDEC fuse numbers including the UES fuses and PTD fuses are shown on the logic diagram.




Note: The development software configures all of the architecture control bits and checks for proper pin usage automatically.



#### Simple Mode Logic Diagram

**DIP, SOIC & PLCC Package Pinouts** 





## Absolute Maximum Ratings<sup>(1)</sup>

| Supply voltage V <sub>cc</sub> –.5 to +7V                        |
|--|
| Input voltage applied $-2.5$ to V <sub>cc</sub> +1.0V            |
| Off-state output voltage applied $-2.5$ to V <sub>cc</sub> +1.0V |
| Storage Temperature65 to 150°C                                   |
| Ambient Temperature with   |

Power Applied .....-55 to 125°C

 Stresses above those listed under the "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress only ratings and functional operation of the device at these or at any other conditions above those indicated in the operational sections of this specification is not implied (while programming, follow the programming specifications). **Recommended Operating Conditions** 

#### Commercial Devices:

| Ambient Temperature (T <sub>A</sub> ) | 0 to 75°C       |
|---------------------------------------|-----------------|
| Supply voltage (V <sub>cc</sub> )     |                 |
| with Respect to Ground                | +4.75 to +5.25V |

#### **DC Electrical Characteristics**

### Over Recommended Operating Conditions (Unless Otherwise Specified)

| SYMBOL      | PARAMETER                         | CONDITION   | MIN.      | TYP. <sup>2</sup> | MAX.  | UNITS |
|-------------|-----------------------------------|---|-----------|-------------------|-------|-------|
| VIL         | Input Low Voltage                 |   | Vss – 0.5 | _                 | 0.8   | V     |
| <b>V</b> ΙΗ | Input High Voltage                |   | 2.0       | _                 | Vcc+1 | V     |
| lı.         | Input or I/O Low Leakage Current  | $0V \leq V_{IN} \leq V_{IL} (MAX.)$                     |           | _                 | -10   | μA    |
| Ін          | Input or I/O High Leakage Current | $3.5V \le V_{IN} \le V_{CC}$                            | _         | _                 | 10    | μΑ    |
| VOL         | Output Low Voltage                | IOL = MAX. Vin = VIL or VIH                             | _         | _                 | 0.5   | V     |
| <b>V</b> он | Output High Voltage               | $I_{OH} = MAX.$ $V_{II} = V_{IL} \text{ or } V_{IH}$    | 2.4       | _                 | _     | V     |
|             |                                   | $I_{OH} = -100 \ \mu A$ $V_{in} = V_{IL} \ or \ V_{IH}$ | Vcc-1     | —                 | _     | V     |
| IOL         | Low Level Output Current          |   | —         | _                 | 16    | mA    |
| ЮН          | High Level Output Current         |   | —         | —                 | -3.2  | mA    |
|             | Output Short Circuit Current      | $V_{CC} = 5V$ $V_{OUT} = 0.5V$ $T_A = 25^{\circ}C$      | -30       | —                 | -150  | mA    |

#### COMMERCIAL

| ISB | Stand-by Power<br>Supply Current  | $V_{IL} = GND$ $V_{IH} = Vcc$ Outputs Open  | Z-12/-15<br>ZD-12/-15 | — | 50 | 100 | μΑ |
|-----|-----------------------------------|---|-----------------------|---|----|-----|----|
| Icc | Operating Power<br>Supply Current | $\label{eq:VIL} \begin{array}{ll} \textbf{V}_{\text{IL}}=0.5 \text{V} & \textbf{V}_{\text{IH}}=3.0 \text{V} \\ \textbf{f}_{\text{toggle}}=15 \; \text{MHz} & \text{Outputs Open} \end{array}$ | Z-12/-15<br>ZD-12/-15 |   | _  | 55  | mA |

1) One output at a time for a maximum duration of one second. Vout = 0.5V was selected to avoid test problems by tester ground degradation. Characterized but not 100% tested.

2) Typical values are at Vcc = 5V and TA = 25  $^\circ\text{C}$ 

## Capacitance ( $T_A = 25^{\circ}C$ , f = 1.0 MHz)

| SYMBOL           | PARAMETER         | MAXIMUM* | UNITS | TEST CONDITIONS                             |
|------------------|-------------------|----------|-------|---|
| C                | Input Capacitance | 10       | pF    | $V_{cc} = 5.0$ V, $V_{l} = 2.0$ V           |
| C <sub>I/O</sub> | I/O Capacitance   | 10       | pF    | $V_{\rm CC} = 5.0$ V, $V_{\rm I/O} = 2.0$ V |

\*Characterized but not 100% tested.



### AC Switching Characteristics

|                           |                         |  | CC   | M    | CC   | ОМ   |       |
|---------------------------|-------------------------|--|------|------|------|------|-------|
|                           | TEST                    | DESCRIPTION  | -12  |      | -15  |      |       |
|                           | COND <sup>1</sup> .     |  | MIN. | MAX. | MIN. | MAX. | UNITS |
| <b>t</b> pd               | А                       | Input or I/O to Combinational Output                             | 3    | 12   | 3    | 15   | ns    |
| tco                       | А                       | Clock to Output Delay  | 2    | 8    | 2    | 10   | ns    |
| tcf <sup>2</sup>          | —                       | Clock to Feedback Delay  | -    | 6    | _    | 7    | ns    |
| <b>t</b> su               | —                       | Setup Time, Input or Feedback before $Clock\uparrow$             | 10   | _    | 15   | —    | ns    |
| <b>t</b> h                | —                       | Hold Time, Input or Feedback after ${\sf Clock} {\uparrow}$      | 0    | _    | 0    | —    | ns    |
|                           | A                       | Maximum Clock Frequency with<br>External Feedback, 1/(tsu + tco) | 55   | —    | 40   | _    | MHz   |
| <b>f</b> max <sup>3</sup> | А                       | Maximum Clock Frequency with<br>Internal Feedback, 1/(tsu + tcf) | 62.5 | _    | 45.5 | _    | MHz   |
|                           | A                       | Maximum Clock Frequency with<br>No Feedback                      | 83.3 |      | 62.5 | _    | MHz   |
| <b>t</b> wh               | —                       | Clock Pulse Duration, High                                       | 6    | _    | 8    | _    | ns    |
| twl                       |                         | Clock Pulse Duration, Low  | 6    |      | 8    | —    | ns    |
| <b>t</b> en               | В                       | Input or I/O to Output Enabled                                   | —    | 12   | _    | 15   | ns    |
|                           | В                       | OE to Output Enabled   | -    | 12   | —    | 15   | ns    |
| <b>t</b> dis              | С                       | Input or I/O to Output Disabled                                  | _    | 15   | _    | 15   | ns    |
|                           | C OE to Output DIsabled |  | -    | 12   | —    | 15   | ns    |
| tas                       | _                       | Last Active Input to Standby                                     |      | 140  | 50   | 150  | ns    |
| <b>t</b> sa⁴              | _                       | Standby to Active Output   |      | 13   | 5    | 15   | ns    |

#### **Over Recommended Operating Conditions**


1) Refer to **Switching Test Conditions** section.

2) Calculated from fmax with internal feedback. Refer to fmax Specification section.

3) Refer to **fmax Specification** section.

4) Add tsa to tpd, tsu, ten and tdis when the device is coming out of standby state.

#### **Standby Power Timing Waveforms**





## AC Switching Characteristics

#### **Over Recommended Operating Conditions**

|                           |                        |  | СОМ  |      | СОМ  |      |       |
|---------------------------|------------------------|--|------|------|------|------|-------|
| PARAMETER                 | TEST                   | TEST DESCRIPTION   | -12  |      | -15  |      |       |
|                           | COND <sup>1</sup> .    |  | MIN. | MAX. | MIN. | MAX. | UNITS |
| <b>t</b> pd               | А                      | Input or I/O to Combinational Output                             | 3    | 12   | 3    | 15   | ns    |
| <b>t</b> co               | А                      | Clock to Output Delay  | 2    | 8    | 2    | 10   | ns    |
| <b>t</b> cf <sup>2</sup>  | —                      | Clock to Feedback Delay  | —    | 6    | —    | 7    | ns    |
| <b>t</b> su               | —                      | Setup Time, Input or Feedback before $Clock\uparrow$             | 10   | _    | 15   | —    | ns    |
| <b>t</b> h                | —                      | Hold Time, Input or Feedback after ${\sf Clock}{\uparrow}$       | 0    | _    | 0    | _    | ns    |
|                           | A                      | Maximum Clock Frequency with<br>External Feedback, 1/(tsu + tco) | 55   | —    | 40   | —    | MHz   |
| <b>f</b> max <sup>3</sup> | A                      | Maximum Clock Frequency with<br>Internal Feedback, 1/(tsu + tcf) | 62.5 |      | 45.5 | _    | MHz   |
|                           | A                      | Maximum Clock Frequency with<br>No Feedback                      | 83.3 |      | 62.5 | _    | MHz   |
| <b>t</b> wh               | _                      | Clock Pulse Duration, High                                       | 6    |      | 8    | _    | ns    |
| twl                       | —                      | Clock Pulse Duration, Low  | 6    | _    | 8    | —    | ns    |
| <b>t</b> en               | В                      | Input or I/O to Output Enabled                                   | _    | 12   |      | 15   | ns    |
|                           | B OE to Output Enabled |  | —    | 12   |      | 15   | ns    |
| <b>t</b> dis              | С                      | Input or I/O to Output Disabled                                  | —    | 15   | _    | 15   | ns    |
|                           | С                      | OE to Output Disabled  | -    | 12   | _    | 15   | ns    |

1) Refer to Switching Test Conditions section.

2) Calculated from fmax with internal feedback. Refer to fmax Specification section.

3) Refer to **fmax Specification** section.




### **Dedicated Power-Down Pin Specifications**

#### **Over Recommended Operating Conditions**

|               |                     |                                  | CC   | M    | C    | MC   |       |
|---------------|---------------------|----------------------------------|------|------|------|------|-------|
|               | TEST                | DESCRIPTION                      | -12  |      | -15  |      |       |
|               | COND <sup>1</sup> . |                                  | MIN. | MAX. | MIN. | MAX. | UNITS |
| <b>t</b> whd  |                     | DPP Pulse Duration High          | 12   | _    | 15   | _    | ns    |
| <b>t</b> wld  |                     | DPP Pulse Duration Low           | 25   | _    | 30   | _    | ns    |
| ACTIVE TO     | STANDB              | 1                                |      |      |      |      |       |
| <b>t</b> ivdh | _                   | Valid Input before DPP High      | 5    | _    | 8    | _    | ns    |
| <b>t</b> gvdh | _                   | Valid OE before DPP High         | 0    | _    | 0    | —    | ns    |
| <b>t</b> cvdh |                     | Valid Clock Before DPP High      | 0    |      | 0    | —    | ns    |
| <b>t</b> dhix |                     | Input Don't Care after DPP High  | _    | 2    | _    | 5    | ns    |
| <b>t</b> dhgx |                     | OE Don't Care after DPP High     | _    | 6    | _    | 9    | ns    |
| <b>t</b> dhcx |                     | Clock Don't Care after DPP High  | _    | 8    | _    | 11   | ns    |
| STANDBY T     | O ACTIVE            |                                  |      |      |      |      |       |
| <b>t</b> dliv |                     | DPP Low to Valid Input           | 12   |      | 15   | _    | ns    |
| <b>t</b> dlg∨ | _                   | DPP Low to Valid $\overline{OE}$ | 16   | _    | 20   | —    | ns    |
| <b>t</b> dlcv | —                   | DPP Low to Valid Clock           | 18   | —    | 20   | -    | ns    |
| <b>t</b> dlov | Α                   | DPP Low to Valid Output          | 5    | 24   | 5    | 30   | ns    |


1) Refer to **Switching Test Conditions** section.


### **Dedicated Power-Down Pin Timing Waveforms**






## Switching Waveforms







**Clock Width** 



**Registered Output** 




OE to Output Enable/Disable



fmax with Feedback




#### fmax Descriptions




fmax with External Feedback 1/(tsu+tco)

**Note:** fmax with external feedback is calculated from measured tsu and tco.



fmax with No Feedback

**Note:** fmax with no feedback may be less than 1/(twh + twl). This is to allow for a clock duty cycle of other than 50%.



#### fmax with Internal Feedback 1/(tsu+tcf)

**Note:** tcf is a calculated value, derived by subtracting tsu from the period of fmax w/internal feedback (tcf = 1/fmax - tsu). The value of tcf is used primarily when calculating the delay from clocking a register to a combinatorial output (through registered feedback), as shown above. For example, the timing from clock to a combinatorial output is equal to tcf + tpd.


## **Switching Test Conditions**

| Input Pulse Levels             | GND to 3.0V   |
|--------------------------------|---------------|
| Input Rise and Fall Times      | 3ns 10% – 90% |
| Input Timing Reference Levels  | 1.5V          |
| Output Timing Reference Levels | 1.5V          |
| Output Load                    | See Figure    |

3-state levels are measured 0.5V from steady-state active level.

#### **Output Load Conditions (see figure)**

| Tes | t Condition | R1   | R2   | CL   |
|-----|-------------|------|------|------|
| A   |             | 300Ω | 390Ω | 50pF |
| В   | Active High | ∞    | 390Ω | 50pF |
|     | Active Low  | 300Ω | 390Ω | 50pF |
| С   | Active High | ∞    | 390Ω | 5pF  |
|     | Active Low  | 300Ω | 390Ω | 5pF  |





#### **Electronic Signature**

An electronic signature word is provided in every GAL16V8Z/ZD device. It contains 64 bits of reprogrammable memory that can contain user defined data. Some uses include user ID codes, revision numbers, or inventory control. The signature data is always available to the user independent of the state of the security cell.

NOTE: The electronic signature is included in checksum calculations. Changing the electronic signature will alter checksum.

#### **Security Cell**

A security cell is provided in the GAL16V8Z/ZD devices to prevent unauthorized copying of the array patterns. Once programmed, this cell prevents further read access to the functional bits in the device. This cell can only be erased by re-programming the device, so the original configuration can never be examined once this cell is programmed. The electronic signature data is always available to the user, regardless of the state of this security cell.

#### **Device Programming**

GAL devices are programmed using a Lattice Semiconductorapproved Logic Programmer, available from a number of manufacturers (see the Development Tools Section of the Data Book). Complete programming of the device takes only a few seconds. Erasing of the device is transparent to the user, and is done automatically as part of the programming cycle.

## Input Transition Detection (ITD)

The GAL16V8Z relies on its internal input detection circuitry to put the device in to power down mode. If there is no input transition for the specified period of time, the device will go into the power down state. Any valid input transition will put the device back into the active state. The first rising clock transition from power-down state only acts as a wake up signal to the device and will not clock the data input through to the output (refer to standby power timing waveform for more detail). Any input pulse widths greater than 5ns at input voltage level of 1.5V will be detected as input transition. The device will not detect any input pulse widths less than 1ns measured at input voltage level of 1.5V as an input transition.

#### **Dedicated Power-Down Pin**

The GAL16V8ZD uses pin 4 as the dedicated power-down signal to put the device in to the power-down state. DPP is an active high signal where a logic high driven on this signal puts the device into power-down state. Input pin 4 cannot be used as a functional input on this device.

#### **Output Register Preload**


When testing state machine designs, all possible states and state transitions must be verified in the design, not just those required in the normal machine operations. This is because, in system operation, certain events occur that may throw the logic into an illegal state (power-up, line voltage glitches, brown-outs, etc.). To test a design for proper treatment of these conditions, a way must be provided to break the feedback paths, and force any desired (i.e., illegal) state into the registers. Then the machine can be sequenced and the outputs tested for correct next state conditions.

The GAL16V8Z/ZD devices includes circuitry that allows each registered output to be synchronously set either high or low. Thus, any present state condition can be forced for test sequencing. If necessary, approved GAL programmers capable of executing test vectors perform output register preload automatically.

#### Input Buffers

GAL16V8Z/ZD devices are designed with TTL level compatible input buffers. These buffers, with their characteristically high impedance, load driving logic much less than traditional bipolar devices. This allows for a greater fan out from the driving logic.


GAL16V8Z/ZD input buffers have latches within the buffers. As a result, when the device goes into standby mode the inputs will be latched to its values prior to standby. In order to overcome the input latches, they will have to be driven by an external source. Lattice Semiconductor recommends that all unused inputs and tri-stated I/O pins for both devices be connected to another active input,  $V_{cc}$ , or GND. Doing this will tend to improve noise immunity and reduce  $I_{cc}$  for the device.



#### **Typical Input Characteristic**




## **Power-Up Reset**



Circuitry within the GAL16V8Z/ZD provides a reset signal to all registers during power-up. All internal registers will have their Q outputs set low after a specified time (tpr,  $1\mu$ s MAX). As a result, the state on the registered output pins (if they are enabled) will always be high on power-up, regardless of the programmed polarity of the output pins. This feature can greatly simplify state machine design by providing a known state on power-up. The timing diagram for power-up is shown below. Because of the

asynchronous nature of system power-up, some conditions must be met to provide a valid power-up reset of the GAL16V8Z/ZD. First, the Vcc rise must be monotonic. Second, the clock input must be at static TTL level as shown in the diagram during power up. The registers will reset within a maximum of tpr time. As in normal system operation, avoid clocking the device until all input and feedback path setup times have been met. The clock must also meet the minimum pulse width requirements.

#### Input/Output Equivalent Schematics





4.75

PT H->L

PT L->H

0

8

300

25 50

Temperature (deg. C)

75 100 125

5.00

Supply Voltage (V)


PT H->L

PT L->H

5.25

5.50

## Typical AC and DC Characteristics



#### Delta Tpd vs Output Loading

10

8

6

4


2

0

-2

0

Delta Tpd (ns)



#### **Delta Tco vs Output Loading**

-

250



### **Typical AC and DC Characteristics**

